

EGGQUALITY 3.0 COMPLETE SETS

EACH SET CAN BE CUSTOMISED AS REQUIRED

MOST POPULAR

| FEATURES | 4001 | 4002 | 4003 | 4004 | 4005 | 4006 | 4007 | 4008 | 4009 | 4010 | 4011 |
|------------------------|------|------|------|------|------|------|------|------|------|------|------|
| HAUGH UNITS | ✓ | ✓ | | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | | ✓ |
| EGG WEIGHT | ✓ | ✓ | | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | | ✓ |
| ALBUMEN HEIGHT | ✓ | ✓ | | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | | ✓ |
| EGGSHELL STRENGTH | | | | ✓ | | ✓ | ✓ | ✓ | ✓ | | ✓ |
| THICKNESS OF EGG SHELL | | ✓ | | | | | ✓ | ✓ | ✓ | | ✓ |
| YOLK COLOR | | | ✓ | | ✓ | ✓ | | ✓ | ✓ | ✓ | ✓ |
| EGG SHAPE | | ✓ | | | | | ✓ | ✓ | ✓ | | ✓ |
| YOLK HEIGHT | | | | | | | | | | ✓ | ✓ |
| SHELL COLOR | | | | | | | | | ✓ | ✓ | ✓ |

ADDITIONALLY TO ALL SETS, 5 MANUAL ENTRIES IN THE SOFTWARE



BRÖRING
Technology GmbH

BRÖRING EGGQUALITY 3.0 DEVICES COMPARED TO OTHERS

| FEATURES | BRÖRING | OTHERS |
|--------------------|---|---|
| EGG WEIGHT | 0g-400g ±0.1g Accuracy | 20g-300g ±0.2g Accuracy |
| ALBUMEN HEIGHT | 2 - 12mm Adjustable ± 0,1mm Accuracy | 3.0 - 15.0mm ±0.2mm Accuracy |
| EGGSHELL STRENGTH | 0 - 150N 0 - 15,3 kgf | 2.0 – 100.0N 0,2 - 10,2 kgf |
| EGGSHELL THICKNESS | 0 - 12.7mm ±0.01mm Accuracy | 0,10 - 0.60mm ±0.02mm Accuracy |
| YOLK COLOR | YolkFan (color scale: 1 - 16) ±0.1 Resolution | YolkFan (color scale: 1 - 16) ±1.0 Resolution |
| YOLK HEIGHT | 10 - 25 mm Adjustable ±0.1mm Accuracy | 5.0-25.0mm ±0.2mm Accuracy |
| EGG YOLK DIAMETER | Manuel Entrée Caliper 0-150mm | 27.0-69.0mm ±1.0mm Accuracy |
| EGG SHAPE | 0-150mm ± 0.02mm Accuracy | ✗ |
| SHELL COLOR | RGB L*a*b* | ✗ |
| EGG YOLK WEIGHT | 0-2000g ±0,1g | ✗ |
| EGG SHELL WEIGHT | 0g-400g ±0.1g Accuracy | ✗ |
| ALBUMEN WEIGHT | calculated automatically Egg - Yolk - Shell | ✗ |
| IMAGE OF THE EGG | Bitmap file for each egg | ✗ |